

Single Lumen Channel Control 2

2mm internal dia<u>meter</u>



For monitoring the cleaning efficacy in flexible endoscopes to EN ISO 15883-5:2005

To be used in conjunction with ParaSure Cleaning Efficacy Indicators

For further information about any of our products, please visit:

www.parasure.co.uk

ParaSure Limited
ParaSure Ltd | Oakendene Estate | West

Sussex | RH13 8AZ

Tel: 07909337261 Website:

www.parasure.co.uk

PARASURE

PS1640p

Single Lumen Channel Control 1